

Supplementary table S1. Technical specification of using Acemedical Acescope

Disposable laryngoscope blades are coated with an anti-fog coating and employ the familiar Macintosh blade technique.

Storage type	Video (MJPEG), Photo (JPG)
Display	2.8", 240(width) X 320 (height)/TFT-LCD
Alarm	Flashing Pink LED before auto shut down.
Power	Lithium-ion battery (3.6Vdc/1900mAh)
Operating/Charging Time	Over 240 min./over 180 min.
Wireless Charger	:Input 100-240V~, 50/60Hz, 1A
Classification	Class II/Type BF applied part: AceBlade /Internally Powered
Applied part	AceBlade